




# BROADWAY V2



|                    |                |                 |                 |
|--------------------|----------------|-----------------|-----------------|
| <b>DISTANCE:</b>   | <b>37 FEET</b> | <b>VOLUME:</b>  | <b>26.45 mL</b> |
| <b>RATIO:</b>      | <b>4.77</b>    | <b>FORWARD:</b> | <b>15.7 mL</b>  |
| <b>DROP BRUSH:</b> | <b>36 FEET</b> | <b>REVERSE:</b> | <b>10.75 mL</b> |
| <b>TANKS:</b>      | <b>KEGEL</b>   | <b>PUMP:</b>    | <b>50μL</b>     |




## FORWARD LOADS DATA

| # | START | STOP | LOADS | MICS | SPEED | BUFF | TANK      | DISTANCE | T.OIL |
|---|-------|------|-------|------|-------|------|-----------|----------|-------|
| 1 | 2L    | 2R   | 2     | 50   | 14    | 3    | A - Kegel | 0 → 2    | 3,700 |
| 2 | 4L    | 4R   | 1     | 50   | 14    | 3    | A - Kegel | 2 → 4    | 1,650 |
| 3 | 5L    | 5R   | 1     | 50   | 14    | 3    | A - Kegel | 4 → 6    | 1,550 |
| 4 | 7L    | 7R   | 2     | 50   | 14    | 3    | A - Kegel | 6 → 10   | 2,700 |
| 5 | 9L    | 9R   | 2     | 50   | 14    | 3    | A - Kegel | 10 → 14  | 2,300 |
| 6 | 11L   | 10R  | 3     | 50   | 18    | 3    | A - Kegel | 14 → 21  | 3,000 |
| 7 | 13L   | 12R  | 1     | 50   | 18    | 3    | A - Kegel | 21 → 24  | 800   |
| 8 | 2L    | 2R   | 0     | 50   | 22    | 3    | A - Kegel | 24 → 31  | 0     |
| 9 | 2L    | 2R   | 0     | 50   | 26    | 3    | A - Kegel | 31 → 37  | 0     |

## REVERSE LOADS DATA

| # | START | STOP | LOADS | MICS | SPEED | BUFF | TANK      | DISTANCE | T.OIL |
|---|-------|------|-------|------|-------|------|-----------|----------|-------|
| 1 | 2L    | 2R   | 0     | 50   | 30    | 3    | A - Kegel | 36 → 31  | 0     |
| 2 | 12L   | 11R  | 1     | 50   | 26    | 3    | A - Kegel | 31 → 27  | 900   |
| 3 | 10L   | 9R   | 3     | 50   | 22    | 3    | A - Kegel | 27 → 18  | 3,300 |
| 4 | 8L    | 8R   | 3     | 50   | 18    | 3    | A - Kegel | 18 → 11  | 3,750 |
| 5 | 7L    | 7R   | 1     | 50   | 18    | 3    | A - Kegel | 11 → 8   | 1,350 |
| 6 | 6L    | 6R   | 1     | 50   | 18    | 3    | A - Kegel | 8 → 6    | 1,450 |
| 7 | 2L    | 2R   | 0     | 50   | 14    | 3    | A - Kegel | 6 → 0    | 0     |



**KEGEL PATTERN LIBRARY APP**



[PATTERNLIBRARY.KEGEL.NET](https://patternlibrary.kegel.net)



SCAN QR CODE TO  
SHARE AND DOWNLOAD  
THIS PATTERN

