

HQ 429 ○ BTR60 PU 2-1-3 ^{WA} 	HQ 429 * HQ P-L 	FDC 429 * ZU 151 ↓-2 ^R 	1R 429 * BTR60 F1ST 2-1-3 ^{WA} 	2R 429 * BTR60 F1ST 2-1-3 ^{WA} 	3R 429 * BTR60 F1ST 2-1-3 ^{WA} 	4R 429 * BTR60 F1ST 2-1-3 ^{WA} 		LOG PAC 	LOG PAC
HQ1 ○ BTR60 PU 2-1-3 ^{WA} 	HQ2 429 * HQ P-L 				LOG PAC 	HQ4 ○ BTR60 PU 2-1-3 ^{WA} 	HQ4 429 * HQ P-L 		LOG PAC
OPA1 ○ BTR60 PU 2-1-3 ^{WA} 	OPA1 429 * OP P-L 	1A1 ● URAL 375 ↓-2 ^R 	1A1 429 D20 152mm W-S 	2A1 ● URAL 375 ↓-2 ^R 	2A1 429 D20 152mm W-S 	1A4 ● URAL 375 ↓-2 ^R 	1A4 429 D20 152mm W-S 	2A4 ● URAL 375 ↓-2 ^R 	2A4 429 D20 152mm W-S
OPB1 ○ BTR60 PU 2-1-3 ^{WA} 	OPB1 429 * OP P-L 	1B1 ● URAL 375 ↓-2 ^R 	1B2 429 D20 152mm W-S 	2B1 ● URAL 375 ↓-2 ^R 	2B2 429 D20 152mm W-S 	1B4 ● URAL 375 ↓-2 ^R 	1B4 429 D20 152mm W-S 	2B4 ● URAL 375 ↓-2 ^R 	2B4 429 D20 152mm W-S
OPC1 ○ BTR60 PU 2-1-3 ^{WA} 	OPC1 429 * OP P-L 	1C1 ● URAL 375 ↓-2 ^R 	1C1 429 D20 152mm W-S 	2C1 ● URAL 375 ↓-2 ^R 	2C2 429 D20 152mm W-S 	1C4 ● URAL 375 ↓-2 ^R 	1C4 429 D20 152mm W-S 	2C4 ● URAL 375 ↓-2 ^R 	2C4 429 D20 152mm W-S
HQ 2 ○ BTR60 PU 2-1-3 ^{WA} 	HQ 2 429 * HQ P-L 				LOG PAC 			OPA4 ○ BTR60 PU 2-1-3 ^{WA} 	OPA4 429 * OP P-L
OPA2 ○ BTR60 PU 2-1-3 ^{WA} 	OPA2 429 * OP P-L 	1A2 ● URAL 375 ↓-2 ^R 	1A2 429 D20 152mm W-S 	2A2 ● URAL 375 ↓-2 ^R 	2A2 429 D20 152mm W-S 			OPB4 ○ BTR60 PU 2-1-3 ^{WA} 	OPB4 429 * OP P-L
OPB2 ○ BTR60 PU 2-1-3 ^{WA} 	OPB2 429 * OP P-L 	1B2 ● URAL 375 ↓-2 ^R 	1B2 429 D20 152mm W-S 	2B2 ● URAL 375 ↓-2 ^R 	2B2 429 D20 152mm W-S 			OPC4 ○ BTR60 PU 2-1-3 ^{WA} 	OPC4 429 * OP P-L
OPC2 ○ BTR60 PU 2-1-3 ^{WA} 	OPC2 429 * OP P-L 	1C2 ● URAL 375 ↓-2 ^R 	1C2 429 D20 152mm W-S 	2C2 ● URAL 375 ↓-2 ^R 	2C2 429 D20 152mm W-S 				
HQ 3 ○ BTR60 PU 2-1-3 ^{WA} 	HQ3 429 * HQ P-L 								
OPA3 ○ BTR60 PU 2-1-3 ^{WA} 	OPA3 429 * OP P-L 	1A3 ● URAL 375 ↓-2 ^R 	1A3 429 D20 152mm W-S 	2A3 ● URAL 375 ↓-2 ^R 	2A3 429 D20 152mm W-S 				
OPB3 ○ BTR60 PU 2-1-3 ^{WA} 	OPB3 429 * OP P-L 	1B3 ● URAL 375 ↓-2 ^R 	1B3 429 D20 152mm W-S 	2B3 ● URAL 375 ↓-2 ^R 	2B3 429 D20 152mm W-S 				
OPC3 ○ BTR60 PU 2-1-3 ^{WA} 	OPC3 429 * OP P-L 	1C3 ● URAL 375 ↓-2 ^R 	1C3 429 D20 152mm W-S 	2C3 ● URAL 375 ↓-2 ^R 	2C3 429 D20 152mm W-S 				
429 ○ BTR60 PU 2-1-3 ^{WA} 	429 * LOG BASE P-S 	429 LOG 1 ↓-2 ^R 	429 LOG 2 ↓-2 ^R 	429 LOG 3 ↓-2 ^R 	429 LOG 4 ↓-2 ^R 	429 LOG 5 ↓-2 ^R 	429 URAL URV ↓-2 ^R 		