

HQ O TAB11A 570D 3-1-3 ^{WA}	HQ 570D # HQ P-L	1BC # 2H 570D U-2 ^A	LDG ● URAL 570D 375 U-2 ^A	570D # LDG BASE P-S	LDG1 ● URAL 570D 375 U-2 ^A	LDG2 ● URAL 570D 375 U-2 ^A	LDG3 ● URAL 570D 375 U-2 ^A	LDG4 ● URAL 570D WAV U-2 ^A	LDG5 ● URAL 570D 6-3-4 ^T
HQ O TAB11 57E 3-1-3 ^{WA}	HQ 57E # HQ P-L	1A 57E M1979 4-2-4 ^{TA}	2A 57E M1979 4-2-4 ^{TA}	3A 57E GM2 4-2-3 ^T	4B 57E P15-M U-3 ^{TA}	5B 57E P15-M U-3 ^{TA}	6B 57E P15-M U-3 ^{TA}	7B 57E P15-M U-3 ^{TA}	8B 57E GSP U-3 ^{TA}
1C 57E PMP U-2 ^A	2C 57E PMP U-2 ^A	3C 57E PMP U-2 ^A	4C 57E PMP U-2 ^A	5C 57E PMP U-2 ^A	6C 57E TRM U-2 ^A	7C 57E TRM U-2 ^A	8C 57E TRM U-2 ^A	9C 57E TRM U-2 ^A	
1D 57E MTU20 10-7-3 ^T	2D 57E MTU20 10-7-3 ^T	3D 57E MTU20 10-7-3 ^T	4E 57E ITR 13-9-3 ^T	5E 57E ITR 13-9-3 ^T	6E 57E ITR 13-9-3 ^T	7E 57E BAT-M U-2 ^T	8E 57E BAT-M U-2 ^T	9E 57E BAT-M U-2 ^T	
HQ O TAB11 57Rcn 3-1-3 ^{WA}	HQ 57Rcn # HQ P-L	1A 57Rcn BMP1 4-2-4 ^{TA}	2A 57Rcn BMP1 4-2-4 ^{TA}	3A 57Rcn TR125 15-9-4 ^T	4A # 2NAR10 57Rcn F1ST 3-1-3 ^{TA}	5A 57Rcn BMP1 4-2-4 ^{TA}	6A 57Rcn BMP1 4-2-4 ^{TA}	7A 57Rcn TR125 15-9-4 ^T	8A # 2NAR10 57Rcn F1ST 3-1-3 ^{TA}
1C 57Rcn # TAB19 57Rcn 1-1-4 ^{WA}	2C 57Rcn # TAB19 57Rcn 1-1-4 ^{WA}	3C 57Rcn # TAB19 57Rcn 1-1-4 ^{WA}	4C 57Rcn # TAB19 57Rcn 1-1-4 ^{WA}	5C 57Rcn # TAB19 57Rcn F1ST 3-1-3 ^{WA}	HQ # M12 S 0-4-17 ^H	1A O M124 5 3-2-24 ^H	2A O M124 5 3-2-24 ^H	3A ▲ M12C 5 1-2-16 ^H	4B ▲ M12C 5 1-2-16 ^H
HQ O TAB11A 570 3-1-3 ^{WA}	HQ 570 # HQ P-L	FDC # 2H 570 U-2 ^A						HQRPLUA2453 570D U-4 ^W	HQRPL 570D # HQ P-L
HQ1 O TAB11A 570 3-1-3 ^{WA}	HQ1 570 # HQ P-L					HQ2 O TAB11A 570 3-1-3 ^{WA}	HQ2 570 # HQ P-L		
BPA1 O TAB11 570 3-1-3 ^{WA}	BPA1 570 # OP P-L	1A1 ● URAL 570 375 U-2 ^A	1A1 152mm 570 D20 W-S	2A1 ● URAL 570 375 U-2 ^A	2A1 152mm 570 D20 W-S	BPA2 O TAB11 570 3-1-3 ^{WA}	BPA2 570 # OP P-L	1A2 570 APRA 40 U-3 ^W	2A2 570 APRA 40 U-3 ^W
BPB1 O TAB11 570 3-1-3 ^{WA}	BPB1 570 # OP P-L	1B1 ● URAL 570 375 U-2 ^A	1B1 152mm 570 D20 W-S	2B1 ● URAL 570 375 U-2 ^A	2B1 152mm 570 D20 W-S	BPB2 O TAB11 570 3-1-3 ^{WA}	BPB2 570 # OP P-L	1B2 570 APRA 40 U-3 ^W	2B2 570 APRA 40 U-3 ^W
BPC1 O TAB11 570 3-1-3 ^{WA}	BPC1 570 # OP P-L	1C1 ● URAL 570 375 U-2 ^A	1C1 152mm 570 D20 W-S	2C1 ● URAL 570 375 U-2 ^A	2C1 152mm 570 D20 W-S	BPC2 O TAB11 570 3-1-3 ^{WA}	BPC2 570 # OP P-L	1C2 570 APRA 40 U-3 ^W	2C2 570 APRA 40 U-3 ^W
HQ3 O MTLB 570 3-1-3 ^{WA}	HQ3 570 # HQ P-L			HQ4 O MTLB 570 3-1-3 ^{WA}	HQ4 570 # HQ P-L				
BPA3 O MTLB 570 3-1-3 ^{WA}	BPA3 570 # OP P-L	1A3 570 S122 4-2-4 ^{TA}	2A3 570 S122 4-2-4 ^{TA}	BPA4 O MTLB 570 3-1-3 ^{WA}	BPA4 570 # OP P-L	1A4 570 S122 4-2-4 ^{TA}	2A4 570 S122 4-2-4 ^{TA}		
BPB3 O MTLB 570 3-1-3 ^{WA}	BPB3 570 # OP P-L	1B3 570 S122 4-2-4 ^{TA}	2B3 570 S122 4-2-4 ^{TA}	BPB4 O MTLB 570 3-1-3 ^{WA}	BPB4 570 # OP P-L	1B4 570 S122 4-2-4 ^{TA}	2B4 570 S122 4-2-4 ^{TA}		
BPC3 O MTLB 570 3-1-3 ^{WA}	BPC3 570 # OP P-L	1C3 570 S122 4-2-4 ^{TA}	2C3 570 S122 4-2-4 ^{TA}	BPC4 O MTLB 570 3-1-3 ^{WA}	BPC4 570 # OP P-L	1C4 570 S122 4-2-4 ^{TA}	2C4 570 S122 4-2-4 ^{TA}		