Dissectible Transformers

Educational Training Equipment for the 21st Century

Bulletin 211G

1290B-6C

Dissectible Transformer

Purpose

The Hampden Model 1290B-6C Dissectible Transformer is a versatile device for teaching transformer principles. It is also useful in the laboratory or shop when a special transformer. DC choke or AC reactor is needed.

Description

The unit consists of a dissectible, three-legged core and a complement of separate coils. The core consists of silicon steel laminations with an aluminum frame making a strong, lightweight structure. The top portion of the core is removable to enable the various coils to be placed on the core. The interfacing between the two core pieces is carefully machined to minimize magnetic leakage. A stud and wing nut hold the core pieces securely together. A complement of core gap-spacers are also provided for operation as a choke or reactor. Furnished complete with cords.

Typical Applications and Uses

- · Study of Electromagnetic Induction
- · Study of Magnetic Fields
- · Study of AC and DC Electromagnetics
- · Magnetization and Demagnetization of Ferrous Materials
- Isolation Transformer 250 VA
- Autotransformer 500 VA
- · Buck-Boost Transformer (using handwound winding - 1/2 volt per turn) -Ratings to several KVA
- DC Choke
- AC Reactor

111324

- Saturable Reactor
- Study of Transformer Theory: **Basic Transformer Action** Voltage, Current and Impedance Ratios **Exciting Current** Saturation and Hysteresis Eddy Currents Efficiency Regulation

The Model HC-1290A has provision for storing the core, coils, and air gap spacers, and has a luggage style handle for convenient portability.



MODEL HC-1290A Storage and Carrying Case Box Dimensions: 15-1/2"W x 7-3/8"H x 20-5/16"L Weight with 1290B-6C: 50 lbs.



Core 1291

Coil 1295





MODEL 1290B-6C shown

Weight: 45 lbs.

Coil 1293

Coil 1296





Coil 1294

Coil 1292

Coil	1297	

MODEL 1290B-6C includes Core 1291 plus the following coils				
Coil No.	Windings	No. Turns	Wire Size	
1292	1-115V	230	#15	
1293	2-115V	230 each	#15	
1295	1-56V	224	#15	
1296	1-56V	224	#15	
1297	1-DC	896	#22	
1294	1-115V	230	#15	
	1-230V	460	#18	

All Hampden units are available for operation at any voltage or frequency





800-253-2133