

OPERATING INSTRUCTIONS FOR WINHOLT SINGLE-DOOR ELECTRIC WARMING CABINET

DIMENSIONS 20"W x 33"D x 67"H

- Use 110 volts only
- TO MAINTAIN HUMIDITY, FILL A SHALLOW PAN WITH WATER IN THE BOTTOM OF THE CABINET
- ALL EQUIPMENT IS TESTED BEFORE DELIVERY BUT SHOULD BE RECHECKED AT LEAST 6 HOURS PRIOR TO USE IN CASE OF MALFUNCTION
- EQUIPMENT MUST BE KEPT DRY AND AWAY FROM MOISTURE
- WHEN USING MULTIPLE PIECES OF ELECTRICAL EQUIPMENT, DO NOT OVERLOAD THE CIRCUIT, THIS MAY CAUSE THE EQUIPMENT TO FAIL